

Pure[®] Charge&Go X.

The ultimate rechargeable RIC.



NEW Inductive Charger – Dehumidifies, fits custom molds, and is backwards compatible with all Signia Li-ion inductive charging hearing aids

Key features

- Most natural own voice and best speech understanding in noise
- Long-lasting, high-quality audio streaming
- Ultra HD e2e and Bluetooth[®] connectivity



Signia App ready

- TeleCare
- Remote control
- Connectivity & streaming




Equipped with Bluetooth



Rechargeable

Available colors



HIGHLIGHTS:

- Advanced, high-tech Bluetooth streaming of music, phone calls, and TV
- 16% smaller hearing aid design
- 20% increased battery capacity
- New rocker switch
- Available in 2 new colors
- Automatic on/off functionality with charger



StreamLine TV
With StreamLine TV, the TV signal is directly streamed into Pure Charge&Go X hearing aids.



StreamLine Mic
The StreamLine Mic enables hands-free audio streaming (phone calls, music, etc.) from any device with Bluetooth connectivity.



miniPocket
Compatible with the miniPocket for patients to control without the app.

Performance levels

7X

5X

3X

sDemo

YOURSOUND TECHNOLOGY allows you to **HEAR WHAT MATTERS** to you.

**ACOUSTIC-MOTION
SENSORS**

**DYNAMIC SOUNDSCAPE
PROCESSING**

**OWN VOICE
PROCESSING**

Type

Performance levels

Picture

Product details

Matrix (2 ccm)

Battery size

Power consumption

Features

Frequency channels/
Compression controls

Hearing programs

e2e wireless

Direct streaming

TwinPhone

TeleCare

Tinnitus therapies

CROS/BiCROS

Rocker switch

Volume control

Rechargeable

T-coil

Battery door on/off function

Audio input

Modifications

Color conversion kit

App/Accessory compatibility

Signia App

StreamLine TV/StreamLine Mic

miniPocket

ConnexxAir

Noahlink Wireless

Programming adapter/cable

Fitting set

Pure Charge&Go X

7X/5X/3X

New!



S 45/108 dB
M 60/119 dB
P 70/124 dB
HP 75/130 dB

Lithium-ion power cell

1.2 - 1.4 mA

7Nx - 48/20
5Nx - 32/16
3Nx - 24/12

6

13

17

19

24

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28

28


28

28

28


28

S-Receiver




Open Click Domes
Double Click Domes
Click Mold (no vent)

M-Receiver




Open Click Domes
Double Click Domes
Click Mold (no vent)

P-Receiver



Double Click Domes
Click Mold (no vent)

HP-Receiver



Custom Shell (no vent)



(13) Ultra HD e2e with binaural audio signal processing
(17) To be activated via push button, Signia App or miniPocket
(19) TeleCare 3.0
(24) Programmable via Connexx
(28) Via direct streaming

NEW
Silver

(Actual size)

